


THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION WHICH IS THE PROPERTY OF MEASUREMENT SPECIALTIES. THIS DOCUMENT MAY NOT, IN WHOLE OR IN PART, BE DUPLICATED, DISCLOSED OR USED FOR ANY PURPOSES, WHATSOEVER, WITHOUT PRIOR WRITTEN PERMISSION OF MEASUREMENT SPECIALTIES.

REVISIONS


EAN/ ECN	REV	DESCRIPTION	DATE	APPROVAL
	D	UPDATE PER EC010709ECR4052	2015-07-15	Celia Hou




SWITCH SPECIFICATION


SWITCH ACTION		SPST
MAX. SWITCHING VOLTAGE (VDC)	100	
(VRMS)	250	
MAX. SWITCHING CURRENT (AMPS)	1.0	
DC CONTACT RATING (WATTS)	15	
MIN. BREAKDOWN VOLTAGE (VDC)	600	
INITIAL CONTACT RESISTANCE (OHMS)	0.25	

SWITCH CLOSED IN HORIZONTAL POSITION



TANK OPENING DETAILS



NEXT ASSY	USED ON	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MM TOLERANCES ON:	CONTRACT NO.		
			PROJECT NO.		
		MATERIAL	DRAFTSMAN	TITLE	
		HOUSING: ACETAL COPOLYMER FLOAT: POLYPROPYLENE, GROMMET EPDM	Mark Fan		
		FINISH	CHECKER	LCS-01	
			Sealy Li		
			RELEASE	DATE	REV
				2015-07-15	D
THIRD ANGLE PROJECTION 			SCALE: 3/2	WEIGHT:	SHEET 1 OF 1