




Part Number : [1462362122](#)

Product Description : Rectangular Near Field Communication (NFC) Antenna, with Ferrite, 34.39mm by 46.10mm by 0.27mm, 102.00mm Cable Length, with Micro-Lock Plus Connector

Series Number : 146236

Status : Active

Product Category : Antennas



Documents & Resources

Drawings

[1462362122 sd.pdf](#)

[1462362131-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[1462360001-AS.pdf](#)

[1462360001-PS.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 2-Methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one per D(2024)7663-DC (21 Jan 2025)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Antennas
Series	146236
Description	Rectangular Near Field Communication (NFC) Antenna, with Ferrite, 34.39mm by 46.10mm by 0.27mm, 102.00mm Cable Length, with Micro-Lock Plus Connector
Component Type	FPC Coil Antenna
Function	Signal
Near Field Communication	Yes
Product Name	NFC Antenna
Protocol	NFC
Type	Internal, NFC Antenna
UPC	193264218547

Electrical

Electrical Connectivity	Copper Flex
-------------------------	-------------

Frequency	13.56 MHz
Inductance	4.20 μ H

Physical

Cable Length	102.00mm
Length	34.39mm
Mounting Style	Adhesive
Net Weight	1.500/g
Packaging Type	PET Film
Thickness	0.27mm
Width	46.10mm

This document was generated on Sep 18, 2025