

RB ST 16-1,5/S - Reducing bridge



3213254

<https://www.phoenixcontact.com/us/products/3213254>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Reducing bridge, pitch: 10 mm, number of positions: 2, length: 37 mm, color: red

Commercial data

Item number	3213254
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z2X
GTIN	4046356701693
Weight per piece (including packing)	5.37 g
Weight per piece (excluding packing)	5.37 g
Customs tariff number	85366990
Country of origin	PL

RB ST 16-1,5/S - Reducing bridge



3213254

<https://www.phoenixcontact.com/us/products/3213254>

Technical data

Product properties

Product type	Reducing bridge
Number of positions	2
Pitch	10 mm

Dimensions

Width	16.1 mm
Height	37.2 mm
Depth	3 mm
Length	37.2 mm
Pitch	10 mm

Material specifications

Color	red (RAL 3001)
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C ()
Permissible humidity (storage/transport)	30 % ... 70 %

RB ST 16-1,5/S - Reducing bridge

3213254

<https://www.phoenixcontact.com/us/products/3213254>



Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 9.0	EC000489
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RB ST 16-1,5/S - Reducing bridge



3213254
<https://www.phoenixcontact.com/us/products/3213254>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com