

6

5

4

3




2

1



APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/13/16	



RECOMMENDED PCB LAYOUT



CONTACT PIN	BRASS	3u" GOLD
INSULATOR	LCP	IVORY
BODY	BRASS	1u" GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Frequency range: DC~6 GHz

Nominal Impedance: 50 Ohms

Proof Voltage: 60 V

VSWR: 1.3 max @ 3 GHz

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	HR	5/13/16
CHECKED	NP	5/13/16
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE RF CONNECTOR, TYPE MHF, 50 OHMS
VERTICAL

SIZE X	PART NO. RF20-08-L-00-50-G	REV. -
REF: S00277T	SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1