

THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.


© COPYRIGHT - By -

NOTES:

- 1 WIRE RED MARKED
2. ASSEMBLIES ARE PACKED ACCORDINGLY TO PACKAGING SPEC 107- 19583
3. ASSY ARE TESTED FOR 100% CONTINUITY



ISOMETRIC VIEW



CUSTOMER PN


09m0840

TE PN

2297200-1

2 PCS	MICRO-MATCH MOW.24P	2
100 mm	24P. RIBBCBL 28AWG P1.27	1
Qty	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	± -

DWN 21OCT2015

SATHISH KUMAR. G

CHK 21OCT2015

G VAN DOREMALEN

APVD 21OCT2015

G VAN DOREMALEN

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

24 POS. MICRO-MATCH CA. MOW-MOW,L=100MM

SIZE

A300779

CAGE CODE

DRAWING NO

C=2297200

RESTRICTED TO

REV A