

Specifications



Photo is representative



Eaton CB211-25

Circuit Breaker, Automotive, type I footprint, 25A, 14 Vdc, Grey UL-Rated 94V-0 thermoplastic housing with gold metal cover (type I) or silver metal cover (type II)

General specifications

PRODUCT NAME	Eaton Bussmann series type I footprint circuit breaker
CATALOG NUMBER	CB211-25
UPC	051712292481
PRODUCT LENGTH/DEPTH	1.5 in
PRODUCT HEIGHT	0.25 in
PRODUCT WIDTH	0.05 in
PRODUCT WEIGHT	0.03 lb
COMPLIANCES	Contact factory RoHS Compliant

Electrical rating

AMPERAGE RATING	25 A
VOLTAGE RATING	14 Vdc

General information

SPECIAL FEATURES	Type I
------------------	--------

Physical details

PACKAGING TYPE	Blister
----------------	---------

Resources

CATALOGS	Bussmann series full line retail catalog no. 5084
	CB211-25~MINI CB TYPE 1 - ATM FOOTPRINT - 25 AMP
	Bussmann series complete full line catalog no. 1007
CERTIFICATION REPORTS	Eaton Bussmann EU Declaration of conformity 93-68-EEC2617
MULTIMEDIA	Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CB211-25

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

