REDUC-M-KV-M25/M20 - Reducing adapter

1647624

https://www.phoenixcontact.com/ae/products/1647624

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Reducing adapter, connecting thread: M25 x 1.5, color: silver-colored, with O-ring



Product description

Reduced M25 to M20

Commercial data

Item number	1647624
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AF7
Product key	AF7DZX
GTIN	4017918941529
Weight per piece (including packing)	18.87 g
Weight per piece (excluding packing)	15.72 g
Customs tariff number	74198090
Country of origin	DE

Downloaded from Arrow.com.

Technical data


Product properties

Product type	Reducing adapter
Seal present	yes

Connection data

Tightening torque	7.5 ... 8 Nm

Dimensions

Dimensional drawing	
Width	30.00 mm
Length	10 mm
Length of the connecting thread	7 mm
Length without connecting thread	3 mm
Diameter	25 mm
Connecting thread diameter	25 mm
Hexagon angular dimension	30 mm
Thread type connection side	M25 x 1.5
Thread pitch	1.5 mm
Thread type on seal side	M20

Material specifications

Color	brass color
Material	Brass, nickel-plated
Seal material	NBR
Housing surface material	Ni

Cable/line

Halogen-free	no

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (Depends on the screw connection used)
Ambient temperature (operation)	-20 °C ... 80 °C


Mounting

Assembly note	With corresponding screw connection: IP68

Downloaded from Arrow.com.

Drawings

Dimensional drawing



Dimensional drawing

Downloaded from Arrow.com.

Classifications

ECLASS

ECLASS-13.0	27140806
ECLASS-15.0	27140806

ETIM

ETIM 9.0	EC000938

UNSPSC

UNSPSC 21.0	31261500

Downloaded from Arrow.com.

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	99541839-5a1d-40d0-b885-cb1c09bf9185

Phoenix Contact 2025 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT Middle East FZ LLC
1201N-1206N, Dubai Science Park Towers – North
P.O. Box 345002, Dubai, United Arab Emirates
(+971) 4 437-0324
info-me@phoenixcontact.com

Downloaded from Arrow.com.