Part Number : 1731070183
Product Description : FCT Mixed Layout D-Sub Crimp Housing, Female, Tin-plated Shell, 17 Circuits Unloaded, 12 Signal Contact Positions, Black Insulator
Series Number : 173107
Status : Active
Product Category : D-Sub Connectors
Engineering Part Number : FL17W5S7-K121



Documents and Resources

Drawings

1731070183_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Connectors
Series	173107
Description	FCT Mixed Layout D-Sub Crimp Housing, Female, Tin-plated Shell, 17 Circuits Unloaded, 12 Signal Contact Positions, Black Insulator
IP Rating	IP20
Magnetic	Yes
Product Name	FCT Products
Type	Mixed Layout
UPC	889056485593

Electrical

Shielded	Yes

Physical

Circuits (Loaded)	0
Circuits (maximum)	17
Color - Resin	Black
Durability (mating cycles min)	500
Gender	Female
Material - Resin	Polybutylene Terephthalate (PBT)
Material - Shell	Steel
Net Weight	11.200/g
Number of Rows	2
Orientation	Straight
Packaging Type	Carton
Panel Mount	Rear

Downloaded from Arrow.com.

Panel Mount Method	Flange
PCB Locator	No
PCB Retention	No
Pitch - Mating Interface	2.84mm
Pitch - Termination Interface	2.84mm
Plating - Shell	Tin
Polarized to Mating Part	Yes
Ports	1
Shell Size	4
Temperature Range - Operating	-55° to +115°C
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20
Wire Size (AWG)	18, 20, 22, 24, 26, 28

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	FCT Mixed Layout D-Sub, Size 4, 17W5, Plug

Use with Part(s)

Description	Part Number
Use With	FCT Coaxial, High Power, High Voltage, or Pneumatic Contacts

Downloaded from Arrow.com.