



High Temperature Resistant Silicone Wire (14AWG 2.5 mm² 1m Red & Black)

SKU:FIT0583

INTRODUCTION

This product is high temperature resistant silicone rubber copper wire with 14AWG and 2.5mm². It is made of fine tin-plated copper material and not easily oxidized. It adopts the process of mutual twisting, which reduces the signal interference and improves the conductive property. The allowable load voltage is AC600V/DC3KV and the load current reaches 55.6A. The insulating layer is a silica gel material with excellent performance. The insulating layer is thin but not easy to be broke down. It has elasticity, toughness and acid and alkali resistance. Normally, it can be used at temperatures from -60 ° C to +200 ° C, can be used for robots, ESC, motors, robot arms, aeromodelling, car models, and ship models which require high wire performance.

NOTE:

- The power supply should not exceed the rated voltage to avoid affecting the wire life.
- It should be avoided using over the temperature range of -60 ° C ~ +200 ° C

FEATURES

- High temperature resistant, low temperature resistant , not easy to breakdown, high voltage and high current resistant

SPECIFICATION

- Rated voltage: AC600V/DC3KV
- Allowable current: 55.6A
- Temperature range: -60 ° C ~ +200 ° C
- Model: 14AWG 2.5 mm²
- Inner core material: 0.08mm (diameter) tinned copper wire
- Insulation material: silica gel

SHIPPING LIST

- High Temperature Resistant Silicone Wire (14AWG 2.5 mm² Red 1m) x1
- High Temperature Resistant Silicone Wire (14AWG 2.5 mm² Black 1m) x1



<https://www.dfrobot.com/product-1759.html> 8-7-18