Data sheet

CTX 502

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



Crimping tools for coaxial connectors
- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Pressing tool, Crimping tool for contacts, Hexagonal crimp
Order No.	9006380000
Type	CTX 502
GTIN (EAN)	4008190123512
Qty.	1 items

Downloaded from Arrow.com.

Data sheet

CTX 502

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	250 mm	Width (inches)	9.8425 inch
Net weight	654.08 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tool for coaxial connectors BNC, TNC and N / AF 9.3	Version	Mechanical, without interchangeable inserts

Description of contact

Type of contact	Coaxial connector

tool data crimping

Hexagon spanner width (A 2)	1.75 mm	Hexagon AF (A)	9.3 mm
Wire end ferrules cross-section, max.	89 mm²	Wire end ferrules cross-section, min.	89 mm²
Diameter of outer sleeve	10.7 mm	Crimping station, width (B 2)	2.3 mm
Crimping station, width (B 1)	12 mm	Crimping type/profile	Hexagonal crimp
Internal contact diameter (D)	2 mm		

Classifications


ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

Downloaded from Arrow.com.

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Downloaded from Arrow.com.