

## Han-Eco 24B-HSE-for SL-M40



Image is for illustration purposes only. Please refer to product description.

Part number	19 43 024 0548
Specification	Han-Eco 24B-HSE-for SL-M40
HARTING eCatalogue	<a href="https://b2b.harting.com/19430240548">https://b2b.harting.com/19430240548</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco <sup>®</sup> B
Type of hood/housing	Hood

### Version

Size	24 B
Version	Side entry
Cable entry	1x M40
Locking type	Single locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

### Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 61984 EN 45545-2 Fire protection on railway vehicles
Approvals	CE

## Commercial data

Packaging size	1
Net weight	156.92 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140180802
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors