
Part Number : 393900102
Product Description : 9.52mm Pitch Beau Eurostyle Fixed Mount PCB Terminal Block, Modular, 2 Circuits
Series Number : 39390
Status : Active
Product Category : Terminal Blocks and Barrier Strip
Engineering Part Number : MX-MSP0200N-0N



Documents and Resources

Drawings

393900102_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39390
Description	9.52mm Pitch Beau Eurostyle Fixed Mount PCB Terminal Block, Modular, 2 Circuits
Application	Wire-to-Board
Component Type	One Piece
Product Name	Eurostyle Fixed Mount
Type	PCB Terminal Blocks and Connectors
UPC	822348022991

Electrical

Current - Maximum per Contact	30.0A
Voltage - Maximum	600V

Physical

Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Entry Angle	Horizontal
Lock to Mating Part	No
Number of Rows	1

Downloaded from Arrow.com.

Orientation	Vertical
Panel Mount	No
PCB Retention	No
PCB Thickness - Recommended	4.00mm
PC Tail Length	5.20mm
Pitch - Mating Interface	9.53mm
Pitch - Termination Interface	9.53mm
Polarized to Mating Part	N/A
Stackable	Yes
Temperature Range - Operating	110°C
Wire Size (AWG)	10, 12, 14, 16, 18, 20, 22, 24, 26, 28, 30
Wire Size mm^2	0.05-2.50

Solder Process Data

Lead-Free Process Capability	WAVE
Max-Cycle	5
Max-Temp	260

Downloaded from Arrow.com.