





OPTIONAL BACK PANEL
 0.100 [2.54] TH'K- ALUMINUM
 0.075 [1.91] TH'K- WHITE STEEL & GALVANEALD
 0.125 [3.18] TH'K- FIBERGLASS

(4) STAINLESS STEEL
 MOUNTING FEET

(4) EACH #10-32 BRASS
 INSERTS, AND STAINLESS
 STEEL FEET SCREWS

(4) ϕ .34 [8.74]

11.84 [300.65]
 11.19 [284.23]

7.01 [178.05]
 BACK VIEW

CLOSED CELL
 NEOPRENE
 GASKET

S. ST'L HINGE



STAINLESS STEEL
 LOCKABLE TWIST LATCH
 LOCATED ON CENTER

(4) EACH #10-32 BRASS
 INSERTS AND PLATED
 CARBON STEEL SCREWS

MATERIAL:

BOX- COMPRESSION MOLDED FIBERGLASS REINFORCED POLYESTER
 COVER- COMPRESSION MOLDED FIBERGLASS REINFORCED POLYESTER
 WINDOWS- POLYCARBONATE

FRONT VIEW
 WITH COVER REMOVED
 AND BACK PANEL SHOWN



PART No. PJ1086T

for more information visit
www.hammfg.com

Data subject to change without notice

Drawing Not to Scale