

Pushbutton, 15.2 mm, quick connector, momentary contact function, 1 NO, bezel green



fields of application

- Mechanical and system engineering
- Model construction
- Home technology

special features

Drucktaster opak, nicht beleuchtbar
 Einbaudurchmesser 15,2, mm
 max. 250 V / 700 mA
 1 Schließer-Kontakt, Ag
 Schraub- oder Flachstecker-Anschluss
 Befestigungstechnik mit Gewinding
 Schutzart IP 40 frontseitig (IP 65 mit Schutzkappe)



description

Pushbutton with mounting hole diameter 15.2 mm

Pushbutton with mounting hole diameter 15.2 mm, solder/quick-connect terminal for 6.3 x 0.8 mm or 2 x 2.8 x 0.8 mm

technical data

➤ general

Bezel color	green
Property of bezel / mushroom	opaque
Collar shape	round
Operating temperature, min.	-25 °C
Storage temperature, min.	-40 °C
Operating temperature, max.	85 °C
Storage temperature, max.	90 °C
illuminated	No
Packaging	Box
Packaging unit	100 pcs.
net weight	5.0 g
Operating life	25,000 cycles
B10	32,500 cycles
Degree of protection, front side, according to DIN EN 60529	IP40 IP65 IP65 with sealing cap
MOQ order	100 pcs.
RoHS compliant	Yes

direct links

➤ RAFI eCatalog

REACH compliant	Yes
> mounting diameters	
Mounting hole	15.2 mm
Mounting depth	21.5 mm
Installation height	8.2 mm
Outside dimension, width	19 mm
> mechanical data	
Actuation function	momentary contact function
Operating force, min.	7.5 N
Operating travel, max.	3 mm
Contact function	1 NO
Contact system	Bridge contact
Contact material	Silver
Fixing	Threaded ring
Terminal on the rear	Flat quick-connect terminal 6.3 x 0.8 / 2 x 2.8 x 0.8
Solderability	No
> electrical data	
Rated voltage, max.	250 V
Rated current, max.	0.7 A