

Important Note

This product is not available in the European Union. If you live in one of these countries, please contact us for further assistance.

Computer Power Cord, NEMA 5-15P to Locking C13 - 10A, 125V, 18 AWG, 3 ft. (0.91 m)

MODEL NUMBER: P006-L03



NEMA 5-15P to C13 power cable ensures a secure connection for all your equipment. Locking C13 connector prevents accidental disconnection.

Features

**NEMA 5-15P to C13 Power Cable Connects Computers, Printers, Servers and Other Equipment**This NEMA 5-15P to C13 power cable is designed for applications that do not require a heavy-duty cable. This UL-listed 5-15P to C13 power cord can be used to power a computer, printer or monitor or attach a server or drive to a UPS system or PDU.

**Locking C13 Connector Helps Prevent Accidental Disconnection and Expensive Downtime**Having a cable come loose accidentally can mean the loss of power and costly downtime. The P006-L03's locking C13 connector protects your critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

**Lifetime Limited Warranty**The P006-L03 is backed by a lifetime limited warranty, ensuring reliability and performance.

Specifications

| OVERVIEW             |                                                   |
|----------------------|---------------------------------------------------|
| UPC Code             | 037332218261                                      |
| Device Compatibility | Computer; Monitor/HDTV; Printer; Server; UPS; PDU |
| Country/Region       | North America                                     |

Highlights

- Recommended for connecting power to computers, servers and other peripherals
- Adds 3-ft. (0.91 m) to your existing power connection to provide more flexibility in placing devices
- NEMA 5-15P to C13 cord is ideal replacement for worn-out or missing cable
- Locking C13 connector maintains secure link to avoid loss of power and costly downtime

Applications

- Connect devices like computers, servers and monitors to a PDU up to 3 ft. away
- Prevent accidental disconnection with the C13 locking connector
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P006-L03 NEMA 5-15P to C13 Computer Power Cord, Locking C13 Connector - 10A, 125V, 18 AWG, 3 ft.

| INPUT                              |                              |
|------------------------------------|------------------------------|
| Maximum Input Amps                 | 10                           |
| Voltage Compatibility (VAC)        | 125                          |
| PHYSICAL                           |                              |
| Plug Color                         | Black                        |
| Cable Jacket Color                 | Black                        |
| Cable Jacket Material              | PVC                          |
| Cable Jacket Rating                | VW-1                         |
| Power Cord Jacket Type             | SJT                          |
| Cable Outer Diameter (OD)          | 7.7mm                        |
| Number of Conductors               | 3                            |
| Wire Gauge (AWG)                   | 18                           |
| Wire Gauge (OD - mm <sup>2</sup> ) | 0.82                         |
| Cable Length (ft.)                 | 3                            |
| Cable Length (m)                   | 0.91                         |
| Shipping Dimensions (hwd / in.)    | 10.00 x 7.09 x 0.50          |
| Shipping Dimensions (hwd / cm)     | 25.40 x 18.01 x 1.27         |
| Shipping Weight (lbs.)             | 0.27                         |
| Shipping Weight (kg)               | 0.12                         |
| ENVIRONMENTAL                      |                              |
| Operating Temperature Range        | -4° to 221°F (-20° to 105°C) |
| Storage Temperature Range          | -4° to 221°F (-20° to 105°C) |
| Operating Humidity Range           | 0% to 65% RH                 |
| Storage Humidity Range             | 0% to 65% RH                 |
| CONNECTIONS                        |                              |
| Side A - Connector 1               | NEMA 5-15P                   |
| Side B - Connector 1               | IEC-320-C13 - LOCKING        |
| FEATURES & SPECIFICATIONS          |                              |
| Antibacterial                      | No                           |
| Angled Plug                        | No                           |
| High Voltage                       | No                           |
| Locking Plug                       | Yes                          |



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

|                                     |                                     |
|-------------------------------------|-------------------------------------|
| Coiled Power Cord                   | No                                  |
| STANDARDS & COMPLIANCE              |                                     |
| Product Certifications              | CSA (Canada); cUL Listed; UL Listed |
| Product Compliance                  | RoHS; REACH                         |
| WARRANTY & SUPPORT                  |                                     |
| Product Warranty Period (Worldwide) | Lifetime limited warranty           |



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.