

696638-1 Product Details

Share Print Email



Active

Ring and Spade Tongue Terminals

KIT-6,5/16,NI+RT555-.375X1.00

696638-1

TE Internal Number: 696638-1

Product Highlights View All

- Terminal Shape = Ring Tongue
- Receptacle Style = Straight
- Body Style = SOLISTRAND
- Barrel Type = Closed Barrel
- Wire/Cable Type = Regular Wire

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Feedback

Documents Features Compliance

Please Note: Use the Product Drawing for all design activity

Product Type Features	
Receptacle Style	Straight
Barrel Type	Closed Barrel
Wire/Cable Type	Regular Wire
Insulation	No
Insulation Support	Non-Insulation Support
Stud Size	5/16 [M8]
Shape	RING-049
Heavy Duty	No
Finish	Tin

Termination Features	
Wire/Cable Size (CMA)	20,800 – 33,100

Dimensions	
Stud Diameter (mm [in])	8.33 [0.328]

Body Features	
Body Style	SOLISTRAND
Wire Range (mm [AWG])	13.00-15.00² [6]
Material	Copper

Contact Features	
Terminal Shape	Ring Tongue

Industry Standards	
Government/Industry Qualification	No
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Packaging Features	
Packaging Method	Loose Piece

Other	
Brand	TE Connectivity

Related Products

Not quite the product you're looking for? Find Similar Products

View Part in Product Feature Selector

Check for Tooling