




Part Number : [5035662302](#)

Product Description : Easy-On FPC Connector,
0.30mm Pitch, Right-Angle, Bottom Contact, 0.95mm
Height, 23 Circuits, Gold over Nickel Plating

Series Number : 503566

Status : Active

Product Category : FFC / FPC Connectors



Documents and Resources

Drawings

[5035662302_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications


[5035660000-A00.pdf](#)

[5035669200-200.pdf](#)

[5035660000-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	FFC / FPC Connectors
Series	503566
Description	Easy-On FPC Connector, 0.30mm Pitch, Right-Angle, Bottom Contact, 0.95mm Height, 23 Circuits, Gold over Nickel Plating
Product Name	Easy-On
UPC	191128129800

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	0.3A
Voltage - Maximum	50V

Physical

Actuator Type	Front Flip
Circuits (Loaded)	23
Color - Resin	Natural

Contact Position	Bottom
Durability (mating cycles max)	10
Mated Height	0.95mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	35.542/mg
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	No
Pitch - Mating Interface	0.30mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	FPC only

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.30mm Pitch Premo-Flex FPC Jumpers with Latching Ears	<u>15032</u>

This document was generated on Apr 23, 2026