

Quick Links[Cross reference](#)[RoHS/LF P/N Search](#)[Industry Standards](#)[Alphabetical List](#)[Documentation](#)[3D model search](#)[Customer drawing search](#)[Multi Selection Search](#)[Search by category](#)

Start > Search=0Q05125100J0G* > 0Q05125100J0G

0Q05125100J0G**0Q05125100J0G - Terminal Blocks : Pluggable socket (male header), 3.5mm pitch, right angle, 5 position**

ACTIVE

[Distributor Stock](#)[Print Datasheet](#)

FCI Brings You More

[Contact our sales/technical support](#)[Sample request](#)[Customer drawing](#)[Environmental Compliance Report](#)**Specifications****Download document**[General](#) [Dimensional](#) [Mechanical](#) [Physical](#) [Electrical](#) [Approvals / Certifications](#) [Mounting](#)**General**

Gender	Socket (male header)
Orientation	Right angle
Packaging	Box
Product Type	Pluggable Socket
Series	OQ
Number of Positions	5

Dimensional

Pitch	3.5 mm
-------	--------

Mechanical

Number of mating cycles	200
-------------------------	-----

Physical

Soldering temperature (celcius)	260 +/- 5 Celcius (5 sec)
Color (Housing)	Green
Material (Housing)	Thermoplastic UL94V-0
Terminal material	Copper
Terminal plating	Tin
Temperature (Operating - range)	-40 to +115 Celcius

Electrical

Withstanding Voltage	1.6 kV
Current rating	10 A
Voltage rating	300 V

Approvals / Certifications

Approvals / Certifications	cULus, VDE
----------------------------	------------

Mounting

Board attachment	TMT
------------------	-----