



APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/23/10	
A		REVISED DIM.	4/16/13	



SPECIFICATIONS:

Material:

Insulator: NY66, rated UL 94V-0

Insulator color: Natural

Electrical:

Voltage rating: 125 V AC/DC

Current rating: 2A AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 800 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 15
A = .079 [2.00] x No. of Spaces
B = .079 [2.00] x No. of Spaces + .114 [2.90]
C = .079 [2.00] x No. of Spaces + .157 [4.00]

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

.079 [2.00] CRIMP HOUSING

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				HOLES			
.X	± .10	ØX	± .10	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010				
APPROVALS				DATE			
DRAWN	AY			11/23/10			
CHECKED	AH			11/23/10			
APPROVED							
TITLE							
.079 [2.00] CRIMP HOUSING							
ADAM TECH							
909 Rayhawk Avenue, Union, NJ 07083							
Phone: 908-687-5000 Fax: 908-687-5710							
SIZE		PART NO.					
X				2CH-F-XX			
REF: S00099T	SCALE: NTS		SHEET 1 OF 1		REV. A		