

Product data sheet

Specifications



APC Performance SurgeArrest 11 Outlet with Phone (Splitter), Coax and Ethernet Protection, 120V

P11VNT3

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Plug standard	NEMA 5-15P
Cable length	2.44 m
Number of cables	1
Provided equipment	6 ft network cable Coaxial cable Cord management straps Telephone cable User manual

Physical

Colour	Black
Height	4 cm
Width	11.9 cm
Depth	30.2 cm
Net weight	1.06 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

Input

Network frequency	50/60 Hz
Switching current capacity	15 A

Output

Number of power socket outlets	11
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS rating	L-N: 400 L-G: 500 N-G: 500
---------------------	----------------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product certifications	CSA NOM
Standards	UL 1363 UL 1449
Equipment protection policy	Lifetime : \$100000

Environmental

Ambient air temperature for operation	0...45 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

Surge Protection and Filtering

Response time	0 ns common mode
Common mode rejection	70 dB
Surge energy rate	3020 J
Data line protection	RJ11 analog phone line for phone/fax/modem/DSL RJ45 network line - 10/100 base-T Ethernet Coaxial cable for CATV/SATV/modem/audio-video

Packing Units

Package 1 Weight	1.35 kg
Package 1 Height	6 cm
Package 1 width	19.2 cm
Package 1 Length	34.5 cm
SCC14	10731304249020
Number of Units in Package 2	6
Package 2 Weight	8.88 kg
Package 2 Height	381.00 mm
Package 2 width	203.20 mm
Package 2 Length	381.00 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	Limited Lifetime
----------	------------------