



Part Number : 1120361000
Product Description : IP20 Unmanaged Ethernet Switch, 5 Ports, 10/100Mb Data Speed
Series Number : 112036
Status : Active
Product Category : Industrial Ethernet Switches
Engineering Number : DRL-250MB



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Industrial Ethernet Switches
Series	112036
Description	IP20 Unmanaged Ethernet Switch, 5 Ports, 10/100Mb Data Speed
Approvals	CE, FCC, UL
Comments	10/100 Base TX (Mbaud)
IP Rating	IP20
Product Family	Industrial Ethernet Switches
Product Name	IP20 Unmanaged Ethernet Switch
Protocol	EtherNet (IEEE 802.3)
Switch Functionality	Unmanaged
UPC	78172561271

Electrical

Data Speed	Fast Ethernet (10/100Mbps)
EMC	CE, EN 610006-2-4, FCC Part 15, ICES-003
Supply Voltage	24V DC

Physical

Ethernet Connector	RJ45
Housing Depth	73.80mm
Housing Length	109.20mm
Housing Width	23.40mm
MAC Address	2048
Mechanical Shock	IEC 60068-2-27
Mounting Style	DIN Rail, Wall
Packaging Type	Carton
Ports	5
Power Input	24V DC
Temperature Range - Operating	-40° to +70°C
Uplink Connection	N/A
Vibration	IEC 60068-2-6

This document was generated on Mar 26, 2024