

M23 06 Female-C



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 106 3101
Specification	M23 06 Female-C
HARTING eCatalogue	https://harting.com/09151063101

Identification

Category	Inserts
Series	Circular connectors M23
Identification	Signal
Element	Inserts

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	6
Details	Please order crimp contacts separately. 6x 2 mm

Technical characteristics

Conductor cross-section	0.75 ... 2.5 mm ²
Rated current	20 A
Rated voltage	300 V
Rated impulse voltage	2.5 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



Pushing Performance
Since 1945

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	White
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	5
Net weight	3.49 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140187030
eCl@ss	27440223 Contact insert for circular connectors
ETIM	EC003557
UNSPSC 24.0	39121421