

Type 12 Mild Steel Miniature Pushbutton Enclosures *MPB Series*



Application

- Designed to accept 22mm miniature oil tight pushbuttons, switches and pilot lights.
- Provides protection from dirt, dust, oil and water.

Standards

- UL 508A Type 12 and 13
- CSA Type 12 and 13
- **Complies with**
 - NEMA Type 12 and 13
 - IEC 60529, IP54
- Appropriate components are required to maintain these standards.

Construction

- Formed 16 gauge steel.
- Smooth continuously welded seams.
- Welded brackets provide for enclosure mounting.
- Captive cover screws thread into sealed wells.
- Larger enclosures provide internally hinged removable covers, designed to hold the cover open during wiring (see table).
- Oil resistant gasket and adhesive.
- A bonding stud is provided on the door and a grounding stud is provided on the enclosure.

Finish

- Offered in 2 colors - Cover and enclosure are phosphatized and finished in (a) ANSI 61 gray or (b) RAL7035 light gray powder coating.

Accessories

- Hole Plugs
- Pedestal and Base
- General Accessories

New and improved PDF part drawing files with more detail now available.

Click part number in table below to access PDF, DXF, and STEP files.

ANSI 61 Gray Part No.	RAL7035 Light Gray Part No.	No. of Holes	H	Enclosure W	D
MPB1 ¹	MPB1LG ¹	1	3.25	2.75	3.50
MPB2 ¹	MPB2LG ¹	2	5.13	2.75	3.50

ANSI 61 Gray Part No.	RAL7035 Light Gray Part No.	No. of Holes	Enclosure		
			H	W	D
MPB3 ¹	MPB3LG ¹	3	7.00	2.75	3.50
MPB4 ¹	MPB4LG ¹	4	8.88	2.75	3.50
MPB6	MPB6LG	6	8.50	5.00	4.25
MPB9	MPB9LG	9	8.50	6.50	4.25
MPB12	MPB12LG	12	10.38	6.50	4.25

¹ Not hinged

Tags: **pushbutton, Type 12, button, dial, switch, pilot light, 22mm**

Data subject to change without notice.

© 2026. Hammond Manufacturing Ltd. All rights reserved.