


REV.	DATE	DESCRIPTION
NC	10/31/01	INITIAL RELEASE



DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY	APPROVALS	DATE	 Connector Corporation					
1 BODY	BRASS	NICKEL	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4	DRAWN G.R.S.	10/31/01	TITLE N PLUG TO MCX JACK ADAPTOR					
2 INSULATOR	TEFLON	NATURAL		CHECKED							
3 CONTACT PIN	BER. COPPER	GOLD		ISSUED							
4 GASKET	SILICONE	RED									
5						SIZE	FSIM NO.	DWG. NO.	REV.		
6						A	99001	242170 DWG	NC		
7						SCALE	NA	PART NO.	242170	SHEET	1 OF 1
8			DO NOT SCALE DRAWINGS								

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN MILLIMETERS
FOR CUSTOMER REFERENCE ONLY

UNLESS OTHERWISE SPECIFIED
TOLERANCES FOR MILLIMETERS ARE:

0.5-6 = ± 0.2
6-30 = ± 0.4
30-120 = ± 0.6
120-315 = ± 1
315-1000 = ± 1.6
1000-2000 = ± 2.4

APPROVALS	DATE
DRAWN G.R.S.	10/31/01
CHECKED	
ISSUED	

TITLE	SIZE	FSOM NO.	DWG. NO.	REV.
N PLUG TO MCX JACK ADAPTOR	A	99001	242170 DWG	NC
SCALE	NA	PART NO.	242170	SHEET 1 OF 1