

Plastic label - US-EMLP (35X15)



0830300

<https://www.phoenixcontact.com/us/products/0830300>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Plastic label, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, lettering field size: 35 x 15 mm, Number of individual labels: 27



Your advantages

- PVC material flammability rating V0 in accordance with UL 94
- The markers, which are supplied as uniform cards, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The perforated markers and labels are easy to separate and can be easily fitted
- The sheets provide space for including function texts
- The US-EMLP ... UniSheet labeling range includes self-adhesive device markers with good adhesive properties

Commercial Data

Item number	0830300
Packing unit	1 pc
Minimum order quantity	10 pc
Sales Key	B12
Product Key	BG2419
Catalog Page	Page 315 (C-3-2019)
GTIN	4046356715157
Weight per Piece (including packing)	18.44 g
Weight per Piece (excluding packing)	17.9 g
Customs tariff number	39199080
Country of origin	DE

Plastic label - US-EMLP (35X15)

0830300

<https://www.phoenixcontact.com/us/products/0830300>



Technical Data

Product properties

Product type	Device marking
--------------	----------------

Marking

Number of individual labels	27
Number of individual labels per row	3

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

Color	white
RoHS compliant	Yes
Foil strength	500 µm
Adhesive strength	50 µm
Adhesive	Acrylic
Material	PVC
Components	Silicone-free
Silicone-free	yes

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S

Plastic label - US-EMLP (35X15)



0830300

<https://www.phoenixcontact.com/us/products/0830300>

Cycles	2
--------	---

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Dimensions

Width	35 mm
Height	0.5 mm
Length	15 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Plastic label - US-EMLP (35X15)

0830300

<https://www.phoenixcontact.com/us/products/0830300>



Approvals



CSA

Approval ID: 70191766

Plastic label - US-EMLP (35X15)

0830300

<https://www.phoenixcontact.com/us/products/0830300>



Classifications

ECLASS

ECLASS-9.0	27400629
ECLASS-10.0.1	27400629
ECLASS-11.0	27281103

ETIM

ETIM 8.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

Plastic label - US-EMLP (35X15)

0830300

<https://www.phoenixcontact.com/us/products/0830300>



Accessories

Magazine

Magazine - THERMOMARK CARD-US-MAG1 - 5146451

<https://www.phoenixcontact.com/us/products/5146451>

Magazine for the THERMOMARK CARD printer, for accommodating US cards



Magazine

Magazine - TMP-US-MAG1 - 0803341

<https://www.phoenixcontact.com/us/products/0803341>

Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards



Plastic label - US-EMLP (35X15)

0830300

<https://www.phoenixcontact.com/us/products/0830300>



Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110-TC - 0801371

<https://www.phoenixcontact.com/us/products/0801371>



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., width: 110 mm, color: black

Ink ribbon cartridge

Ink ribbon cartridge - TMP-RIBBON 110 BK 100 - 0803374

<https://www.phoenixcontact.com/us/products/0803374>



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups UCT. ..., US..., and UM..., width: 110 mm, color: black

Plastic label - US-EMLP (35X15)

0830300

<https://www.phoenixcontact.com/us/products/0830300>



Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110/50-TC - 0801384

<https://www.phoenixcontact.com/us/products/0801384>



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., width: 110 mm, color: black

Ink ribbon cartridge

Ink ribbon cartridge - TMP-RIBBON 110 BK 101 - 0803714

<https://www.phoenixcontact.com/us/products/0803714>



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)..., US-TM(F)L..., US-WMTB..., US-EML..., US-EML(S)P..., US-EMLP-HA..., US-EM(S)P..., US-EML-RS..., width: 110 mm, color: black

Plastic label - US-EMLP (35X15)

0830300

<https://www.phoenixcontact.com/us/products/0830300>



Ink ribbon cartridge

Ink ribbon cartridge - TMP-RIBBON 110 BU 100 - 0803378

<https://www.phoenixcontact.com/us/products/0803378>



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)...., US-TM(F)L...., US-WMTB...., US-EML...., US-EML(S)P...., US-EMLP-HA...., US-EM(S)P...., US-EML-RS...., width: 110 mm, color: blue

Ink ribbon cartridge

Ink ribbon cartridge - TMP-RIBBON 110 GN 100 - 0803380

<https://www.phoenixcontact.com/us/products/0803380>



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)...., US-TM(F)L...., US-WMTB...., US-EML...., US-EML(S)P...., US-EMLP-HA...., US-EM(S)P...., US-EML-RS...., width: 110 mm, color: green

Plastic label - US-EMLP (35X15)

0830300

<https://www.phoenixcontact.com/us/products/0830300>



Ink ribbon cartridge

Ink ribbon cartridge - TMP-RIBBON 110 RD 100 - 0803377

<https://www.phoenixcontact.com/us/products/0803377>

Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)...., US-TM(F)L...., US-WMTB...., US-EML...., US-EML(S)P...., US-EMLP-HA...., US-EM(S)P...., US-EML-RS...., width: 110 mm, color: red



Ink ribbon cartridge

Ink ribbon cartridge - TMP-RIBBON 110 YE 100 - 0803379

<https://www.phoenixcontact.com/us/products/0803379>

Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)...., US-TM(F)L...., US-WMTB...., US-EML...., US-EML(S)P...., US-EMLP-HA...., US-EM(S)P...., US-EML-RS...., width: 110 mm, color: yellow



Plastic label - US-EMLP (35X15)

0830300

<https://www.phoenixcontact.com/us/products/0830300>



Ink cartridge

Ink cartridge - BM ID-CARTR. BK - 1044345

<https://www.phoenixcontact.com/us/products/1044345>



Replacement UV fluid, 23 ml, color: black

Ink cartridge

Ink cartridge - BM ID-CARTR. CY - 1044346

<https://www.phoenixcontact.com/us/products/1044346>



Replacement UV fluid, 23 ml, color: cyan

Plastic label - US-EMLP (35X15)

0830300

<https://www.phoenixcontact.com/us/products/0830300>



Ink cartridge

Ink cartridge - BM ID-CARTR. YE - 1044348

<https://www.phoenixcontact.com/us/products/1044348>

Replacement UV fluid, 23 ml, color: yellow



Magazine

Magazine - BM ID-ADAPTER PLATE-US - 1044355

<https://www.phoenixcontact.com/us/products/1044355>

Adapter plate for accommodating US sheets



Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com