



Part Number : [731010040](#)
Product Description : BNC Jack, Right-Angle, Bulkhead Receptacle, PCB, with Board Lock Legs, Die Cast Body, Housing Height 15.93mm, Nut and Lockwasher Not Included, Bag, 75 Ohms
Series Number : 73171
Status : Active
Product Category : RF / Coaxial Connectors



Documents & Resources

- Drawings**
[731010040 sd.pdf](#)
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

- Compliance Statements
- EU RoHS
 - REACH SVHC
 - Low-Halogen
- Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73171
Description	BNC Jack, Right-Angle, Bulkhead Receptacle, PCB, with Board Lock Legs, Die Cast Body, Housing Height 15.93mm, Nut and Lockwasher Not Included, Bag, 75 Ohms
Application	RF
Comments	15.93mm Profile
Product Name	BNC
Style	PCB
Type	Miniature
UPC	800753680616

Agency

CSA	LR19980
UL	E107635

Electrical

Frequency	2 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	N/A
Flammability	94V-2
Gender	Jack
Keying to Mating Part	N/A
Net Weight	19.817/g
Orientation	Right Angle
Packaging Type	Bag
Panel Mount	Yes
Panel Mount Method	Bulkhead
PCB Mounting	Through Hole
PCB Thickness - Recommended	3.20mm
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Lead-Free Process Capability	WAVE
Max-Cycle	3
Max-Temp	245

This document was generated on Sep 22, 2025