



**Part Number :** [1300940497](#)

**Product Description :** Bus-Drop Support Grip,  
Single "U" Eye, Cable Diameter 17.78-21.59mm  
(.700-.850"), Approximate Break Strength 861.83kg  
(1900 lbs)

**Series Number :** 130094

**Status :** Active

**Product Category :** Cable Grips

**Engineering Number :** 36569



---

## Documents & Resources

### Drawings

[1300940497\\_sd.pdf](#)

[PK-130227-004-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Cable Grips
Series	130094
Description	Bus-Drop Support Grip, Single "U" Eye, Cable Diameter 17.78-21.59mm (.700-.850"), Approximate Break Strength 861.83kg (1900 lbs)
Product Name	Bus-Drop
Type	Support Grip
UPC	78678836569

### Agency

CSA	LR32159
UL	E76954

### Physical

Approximate Break Strength	861.83kg (1900 lbs)
Bale Length	0.229m (9.00")
Body Style	Straight
Cable Diameter	17.78-21.59mm (.700-.850")
Color - Grommet	N/A
Eye Type	Single
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.216m (8.50")
Net Weight	47.785/g

Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

---

This document was generated on Sep 13, 2025