232268-000 | TDUX-100-INT



TDUX - Inflatable Duct Seal, Size 100

- Flexible and reliable wraparound inflatable sealing system for cables
- Fast and easy to install or remove, even when water is flowing out of the duct
- Independent of duct or cable ovality
- Water and airtight up to 50 kPa (7 psi)
- Environmentaly friendly, non-toxic and resistant to chemicals

Product Classification

Regional Availability	EMEA
Product Type	Cable duct seal
Product Series	TDUX
Ordering Note	When sealing more than two cables in a duct, seperate orderable TDUX-CL clips are to be used

Dimensions

Width	120 mm | 4.724 in
Length	482 mm | 18.976 in
Cable Diameter, maximum	90 mm | 3.543 in
Cable Diameter, minimum	45 mm | 1.772 in
Conduit Inner Diameter, maximum	110 mm | 4.331 in
Conduit Inner Diameter, minimum	75 mm | 2.953 in


Dimension Drawing

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 2, 2024

COMMSCOPE®

Downloaded from Arrow.com.

232268-000 | TDUX-100-INT



Environmental Specifications

Installation temperature	-5 °C to +40 °C (+23 °F to +104 °F)

Packaging and Weights

Included	Inflatable bladder with sealing mechanism
Packaging quantity	10

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 2, 2024

COMMSCOPE®

Downloaded from Arrow.com.