NEUTRIK



NADITBNC-F

Female XLR chassis connector 110 Ω input - female BNC 75 Ω output. Interface balanced and coaxial lines.

Features & Benefits

- Allow long cable runs for digital audio signals via low attenuation coax lines
- Match balanced to coaxial lines
- Match impedances 110 Ω to 75 Ω
- Simple to use, passive units

Technical Information

Product	
Title	NADITBNC-F
Connection Type	Adapter
Gender	female

All rights reserved / 23.08.2026

Downloaded from Arrow.com.

NEUTRIK

Electrical	
Frequencyrange	0.1 - 6 MHz
Rated voltage	≤ 5 V p-p
VSWR	< 1.1
Return loss	> 26.4 dB
Insertion Loss	< 0.3 dB @ 0.1 MHz to 10 MHz

Mechanical	
Wiresize	

All rights reserved / 23.08.2026

Downloaded from Arrow.com.