

BU-P3264**(Threaded Banana Plug with Solder Lug)**

- The BU-P3264 is an 8-32 threaded banana (4mm) plug.
- Overall length 1.22" (39.98mm), jack length = 0.56" (14.22mm)
- Compatible with solder connections.
- Material: Body Nickel-plated brass
 Jacks Nickel-plated beryllium copper
- Ratings: Current 15 Amps
 Voltage Hands-free to 5000 VRMS
 Temperature -50°C to 150°C
- RoHS 3 compliant, exemption 6c