

XGS 32000

CMOS Image Sensor, 32.5 Mp, Global Shutter

Product Overview

For complete documentation, see the data sheet.

Advance Information

The XGS 32000 is a 32.5 Mp (6580 x 4935) CMOS image sensor in Super 35 mm optical format, supporting up to 53 frame per second readout with 12-bit output at full resolution, and up to 80 fps with 6K (6144 x 3160) ROI output.

The device provides high resolution, global shutter imaging with high readout speed and a low power footprint for industrial imaging customers. Three speed grades are available to match device output to key computer interfaces and application requirements.

The XGS 32000 shares a common design and footprint with other members of the XGS family, such as the XGS 45000 or XGS 30000, allowing one camera design to support multiple resolutions to simplify and speed time to market for new camera designs.

The XGS 32000 is available in a 251-pin μ PGA package in both monochrome and Bayer color configurations.

Features

- Advanced 3.2 μ m global shutter pixel
- Available speed grades
- Energy efficient design

Applications

- Image capture

Benefits

- High resolution with high image quality and uniformity
- Match to key computer interfaces and application requirements
- Reduced power and thermal footprints

End Products

- Industrial cameras and systems
- Inspection system (food, bottles, recycling labels, etc.)
- Security cameras and systems
- Machine Vision camera
- Broadcasting

Part Electrical Specifications												
Product	Pricing (\$/Unit)	Compliance	Status	Type	Megapixels	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (μ m)	Output Interface	Color	Package Type
NOIX0SE032KB-GTI		<div><div>Pb</div><div>H</div></div>	Active	CMOS	32.5	53	APS-C	Global Shutter	3.2 x 3.2	HiSPi™	RGB	CPGA251 44.40x37.25
NOIX0SN032KB-GTI		<div><div>Pb</div><div>H</div></div>	Active	CMOS	32.5	53	APS-C	Global Shutter	3.2 x 3.2	HiSPi™	Mono	CPGA251 44.40x37.25
NOIX1SE032KB-GTI		<div><div>Pb</div><div>H</div></div>	Active	CMOS	32.5	35	APS-C	Global Shutter	3.2 x 3.2	HiSPi™	RGB	CPGA251 44.40x37.25
NOIX1SN032KB-GTI		<div><div>Pb</div><div>H</div></div>	Active	CMOS	32.5	35	APS-C	Global Shutter	3.2 x 3.2	HiSPi™	Mono	CPGA251 44.40x37.25