


APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	7129	RELEASED	12/13/06	
A		REDRAWN	12/3/12	
B		UPDATE SPEC.	6/20/19	LHT/TW



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

- Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0
- Insulator color: Black
- Contacts: Phosphor Bronze
- Contact Plating: Gold over Nickel underplate on contact area
- Gold flash over Nickel underplate on solder tails
- Electrical: Voltage Rating: 150 VAC max
- Current rating: 1.5 Amps max
- Contact Resistance: 20 mohms max.
- Insulation resistance: 500 Mohms min @500 VDC
- Dielectric withstanding voltage: 1000 Vrms for 1 minut
- Temperature Rating: Operating temperature: -40°C to +85°C
- Environmental: Lead free, RoHS compliant.

ADAM TECH 909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000
 Intercconnects Fax: 908-687-5710

TELEPHONE JACK, SMT, SIDE ENTRY, 6P6C

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED	
.X INCHES	±.10
.XX	±.020
.XXX	±.015
ØXX	±.10
ØXXX	±.015
ØXXXX	±.010
APPROVALS	DATE
DRAWN	BW
CHECKED	
APPROVED	
DATE	12/13/06

TITLE	SIZE	PART NO.	REV.
TELEPHONE JACK, SMT, SIDE ENTRY, 6P6C	X	MT-J-66YX1	B
REF: S0006T	SCALE: NTS	SHEET 1 OF 1	

