




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H	REVISED PER ECR-15-017683	07DEC2015	NL	RS



RECOMMENDED STRIP LENGTH
FOR STANDARD COAX CABLE



RECOMMENDED STRIP LENGTH
FOR ARMOR CABLE


OBSOLETE	RG-142 B/U CABLE $\triangle 6$	225592-2	-	-	225560-2	1-225343-2	227560-1	1-225744-5
	$\triangle 1 \triangle 2 \triangle 3 \triangle 4$	-	225326-2	225325-2	1-331987-9	226719-2	225745-3	225744-8
OBSOLETE	RG-302/U CABLE $\triangle 5$	225592-3	-	-	1-225560-5	1-225343-0	227560-2	225744-6
$\triangle 8$ OBSOLETE	RG-59/U CABLE $\triangle 5$	225592-3	-	-	225560-3	1-225343-0	227560-2	225744-4
	$\triangle 1 \triangle 2 \triangle 3 \triangle 4$	-	9-225326-0	9-225325-0	9-331987-5	226719-2	9-225745-0	225744-3
OBSOLETE	RG-9/U,9A/U,9B/U,& 214/U CABLE $\triangle 3$	332022	-	-	331987	225753-2	225745-1	225744-2
	FOR USE WITH	$\textcircled{6}$ SEAL QTY=1	$\textcircled{5}$ FERRULE ARMOR QTY=1	$\textcircled{4}$ FERRULE BRAID QTY=1	$\textcircled{3}$ FERRULE QTY=1	$\textcircled{2}$ CONTACT QTY=1	$\textcircled{1}$ PLUG ASSY QTY=1	PART NUMBER

53.59[2.110]	17.48[.688]	9.53[.375]	12.70[.500]	1-225744-5
57.94[2.281]	22.25[.876]	12.70[.500]	17.48[.688]	225744-8
53.59[2.110]	14.30[.563]	6.35[.250]	9.53[.375]	225744-6
53.59[2.110]	14.30[.563]	7.92[.312]	9.53[.375]	225744-4
57.94[2.281]	22.25[.876]	12.70[.500]	17.48[.688]	225744-3
57.94[2.281]	22.25[.876]	12.70[.500]	17.48[.688]	225744-2

D	C	B	A	PART NUMBER
---	---	---	---	----------------

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	0.41 [.016]
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH	±	-

MATERIAL

-

FINISH

-

DWN S.D.KOHL 06-05-91

CHK M. SNEED 10-1-91

APVD R. HENRY 10-1-91

PRODUCT SPEC

108-12066

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME

PLUG, WEATHERPROOF,
SERIES HN

-

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=225744

RESTRICTED TO

-

SCALE

2:1

SHEET

1 OF 1

REV

H