Product Line

- DeepTronica
- Single Pair Ethernet
- ZConnect
- Ceres
- X-Lok
  - Accessory
  - Middle Size
  - Mini Size
  - Large Size
  - Standard Size
- M Series
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub





AU-08BMMB-QL8AP0

- Operating Temperature: -40°C ~ +105°C
- Transmission Speed: N/A
- Shielded: Plastic, Non-shielded
- Jacket Material: N/A
- Certificate: N/A

You must login first for view the price


Quantity − 1 +

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type ▾ Search



X-Lok, Mini Size,...	X-Lok, Mini Size,...	X-Lok, Mini Size,...	X-Lok, Mini Size,...	X-Lok, Mini Size,...	X-Lok, Mini Size,...
AB-AU08FL-AUFL... -20°C ~ +80°C	AB-AU08FL-AUFL... -20°C ~ +80°C	AB-AU08FL-AUFL... -20°C ~ +80°C	AB-AU08FL-AUFL... -20°C ~ +80°C	AB-AU08FL-AUFL... -20°C ~ +80°C	AB-AU08FL-AUFL... -20°C ~ +80°C
− 0 +	− 0 +	− 0 +	− 0 +	− 0 +	− 0 +


Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current **2A**	Connector Type **Field Installable**
Shielded **Plastic, Non-shielded**	No. of Contacts **08**
Connector Gender **Male**	Backshell **Straight**
Mating Style **Push Lock**	IP Rating **IP68**
Assembly Style **Screw-in**	

More Options

People Also Bought



AU-08BMMB-QL8AP0	DCD-12AFFM-QL8F04	BB-04AFFM-QR8D05	AB-BB04ML-BBFR-...	M12D-05BFFA-...

Downloaded from Arrow.com.