

External 36V 2U Rack/Tower Battery Pack for Select UPS Systems (BP36V15-2U)

MODEL NUMBER: BP36V15-2U



Highlights

- Extends the runtime of compatible 36V UPS Systems
- Supports 2U rack-mount installation; 4-post installation accessories included
- Options for 2-post rack-mount, tower and wall-mount installation available

Package Includes

- BP36V15-2U external battery pack with attached DC cabling
- 4 post compatible mounting hardware
- Owner's manual

Description

BP36V15-2U rack/tower external battery pack offers extended battery runtime when used in conjunction with expandable 36V rack-mount and tower UPS systems. Includes heavy-gauge cabling with high-current DC connector for safe, simple installation. Included mounting accessories support 2U rack-mount installation in 4-post racks. Options for 2-point front-rail mounting, 2-post center-mounting, wall-mount and upright tower installation available.

Compatible with SMART1200XLHG, SMART1500RML2Ua, SMART1500XL, SMX1200XLHG, SMX1500XLRT2U and other UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible 36V DC UPS systems
- Includes heavy-gauge cabling with high-current DC connectors for simple installation
- Included mounting brackets support rack-mount installation in 4-post racks using only 2 rack spaces (2U)
- UPDHDEARKIT option supports two-point front-rail rack-mount installation without rear supports
- 2POSTRMKITWM option supports balanced two-point center-mounting in 2-post equipment racks
- 2POSTRMKITWM option also enables wallmount installation
- 2-9USTAND option enables upright tower placement
- NOTE: LIMIT OF 1 BP36V15-2U PER UPS, SEE BP36V42-3U or BP36V27-2US FOR MULTI-PACK COMPATIBILITY

Specifications

OVERVIEW	
UPC Code	037332119919
INPUT	
Input Phase	Single-Phase



Powering Business Worldwide

TRIPP LITE
SERIES

BATTERY	
DC System Voltage (VDC)	36
UPS Connection	Grey 2-point connector
Typical Battery Lifespan	4-6 years typical
PHYSICAL	
Material of Construction	Steel
Rack Height	2U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2POSTRMKITWM); 4 post rackmount short-depth (4POSTRAILKITWM); Tower (2-9USTAND); Wallmount (2POSTRMKITWM)
Minimum Required Rack Depth (cm)	43.18
Minimum Required Rack Depth (inches)	17
Optional Mounting Accessory Notes	Optional 2-9USTAND ; enables upright tower UPS placement; 2POSTRMKITWM ; enables wall-mount and 2-post rackmount installation; 4POSTRAILKITWM ; enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm)
Shipping Dimensions (hwd / in.)	8.90 x 20.20 x 23.40
Shipping Dimensions (hwd / cm)	22.61 x 51.31 x 59.44
Shipping Weight (lbs.)	57.81
Shipping Weight (kg)	26.22
Unit Dimensions (hwd / in.)	3.500 x 17.500 x 13.250
Unit Dimensions (hwd / cm)	8,89 x 44,45 x 33,66
Unit Weight (lbs.)	45
Unit Weight (kg)	20.41
Mounting Details	Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.