

MICRO SWITCH



FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING


V3-3015

CK-X3270



NOTE -
I - TERMINALS ARE PLATED FOR SOLDERING

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CHARACTERISTICS

OPERATING FORCE --- 150 GRAM MAX
RELEASE TRAVEL --- .010 MIN
RELEASE FORCE --- 15 GRAM MIN
DIFFERENTIAL TRAVEL --- .002-.010
OVERTRAVEL --- .050 MIN
FREE POSITION --- .625 MAX

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L83
15.1A 1/2HP 125 OR 250 VAC
1/2A 125 VDC, 1/4A 250 VDC
5A 125 VAC "L"



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/.04	X	0.8/.03
ONE PLACE	X.X	0.4/.016	X.X	0.38/.015
TWO PLACES	X.XX	0.15/.006	X.XX	0.13/.005
THREE PLACES	X.XXX		X.XXX	
ANGLES				

SI METRIC
DESIGN UNITS ☐

US CUSTOMARY
☒

WEIGHT

V3-3015

M

DRAWING
NUMBER

2

X

5

ISSUE

8

CHECK

REVISIONS

A

CO

38059

GLH

3 FEB 77

B

CO55729

K E W

28 AUG 84

C

CO

56987

SMA

1 OCT 85

D

CO76103

L J F

4 OCT 93

CHECK

22 APR 76

C E B

CHECK

22 APR 76

GLH

FO-52848-A
DRAWN