



Have a Question?
Chat with a Product
Information Specialist

What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

Home > Products > Input/Output (Box to Box) > Product Feature Selector > Product Details

2227669-3 Product Details

Share Print Email

2227669-3

TE Internal Number: 2227669-3

Preliminary

Pluggable Connectors, Cages & Accessories

Not reviewed for RoHS Compliance

Product Highlights:

- zQSFP+ Product Line
- Cage Assembly with Integrated Connector
- zQSFP+ Application
- Connector Style = Receptacle
- Cage Type = Stacked

[View all Features](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Feedback

Documentation & Additional Information	
Product Drawings: CAGE AND CONNECTOR ASSEMBLY, WITH EMI SPRING FINGERS... (PDF, English) Catalog Pages/Data Sheets: - None Available Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: - None Available List all Documents	Related Products: Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - Product Line = zQSFP+ - Product Type = Cage Assembly with Integrated Connector Mechanical Attachment: - PCB Mount = Single Sided - Bezel Mounting Style = Through Bezel Electrical Characteristics: - Data Signal Rate (Gb/s) = Up to 100 Termination Features: - Termination Method to PC Board = Through Hole - Press Fit Dimensions: - Tail Length (mm [in]) = 2.7 [0.1063] - PCB Thickness, Recommended (mm [in]) = 1.57 [0.062] - Length (X-Axis) (mm [in]) = 73.53 [2.895] - Width (Z-Axis) (mm [in]) = 21.45 [0.845] - Profile Height (Y-Axis) (mm [in]) = 27.10 [1.067] Body Features: - Integrated Light Pipes = Yes Contact Features: Contact Plating, Mating Area, Material = Gold - Tail Plating Material = Gold - Contact Base Material = Copper Alloy - Contact Plating, Mating Area, Thickness (µm [µin]) = 0.76 [29.92] - Underplate Material = Nickel Silver Alloy	Housing Features: - Connector Style = Receptacle Cage Type = Stacked Configuration Features: - Port Configuration = 2x1 - Lightpipe = With - Lightpipe Configuration = Outer, Left Indicator Up - EMI Containment = EMI Springs Industry Standards: RoHS/ELV Compliance = Not reviewed for ELV/RoHS compliance Lead Free Solder Processes = Not reviewed for lead free solder process Conditions for Usage: - Applies To = Printed Circuit Board Operation/Application: Application = zQSFP+ - Heat Sink Application = No Other: - Brand = TE Connectivity

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed