Data sheet

SH 1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Version	Busbar support, beige, 100 °C, Width: 26 mm, V-2, Polyamide 66, when screwed in
Order No.	0299860000
Type	SH 1
GTIN (EAN)	4008190135133
Qty.	20 items

Downloaded from Arrow.com.

Data sheet

SH 1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	24 mm	Depth (inches)	0.9449 inch
Height	24.5 mm	Height (inches)	0.9646 inch
Width	26 mm	Width (inches)	1.0236 inch
Net weight	2 g		

Temperatures

Ambient temperature	-50 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Polyamide 66	Surface finish	all others
Colour	beige	UL 94 flammability rating	V-2

Additional technical data

Installation advice	Direct mounting	Type of mounting	when screwed in

Conductors for clamping (rated connection)

Type of connection	Miscellaneous

General

Number of poles	1	Installation advice	Direct mounting
Operating temperature range, max.	100 °C	Surface finish	all others

Classifications

ETIM 8.0	EC001166	ETIM 9.0	EC001166
ETIM 10.0	EC001166	ECLASS 14.0	27-40-06-07
ECLASS 15.0	27-40-06-07		

Downloaded from Arrow.com.