


Series
MPX

SIZE 22 REAR RELEASE, REAR REMOVABLE CRIMP SOCKET CONTACT

Issue:
Dec. 14, 2018

Page
1/1



MATERIAL :

CONTACT BODY : BERYLLIUM COPPER PER ASTM B 196
PROTECTIVE SLEEVE : STAINLESS STEEL

FINISH :

CONTACT BODY : PLATING .00005 INCH OF GOLD PER SAE AMS-2422 OVER NICKEL PER AMS 2403
PROTECTIVE SLEEVE : PASSIVATED

WIRES ACCOMODATED : AWG 22, 24 AND 26

INSULATION DIAMETER : Ø1,37 (.054) MAX ; Ø 0,66 (.026) MIN
STRIP LENGTH : 3,50 (.137)


TOOLING :

CRIMPING TOOL : M22520/2-01 (RADIAL 282281)
SELECTOR POSITION : 4 FOR AWG 22
3 FOR AWG 24 AND 26

POSITIONER : M22520/2-23 (RADIAL 282970).

INSERTION AND EXTRACTION TOOL : M81969/1-01 (RADIAL 282885) OR M81969/14-01 (RADIAL 282522)

DIMENSIONS : mm (inch are given for information only)



Estimated weight : 0,15 g

CREATION

PEN:

NOM: FALETTI

DATE: Jan. 20, 1988

APPR.: /

Dec. 14, 18

Updated with new template

Branjonneau V.

Perrin H.

Issue

Revisions

Name

Approved

618300EN

RADIAL PROPRIETARY INFORMATION

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from RADIAL. This information is given as an indication. In the continual goal to improve our products, we reserve the right to make any modifications judged necessary.

4112_9311