

Part Number : [936000022](#)

Product Description : Heavy-Duty Metal Cable Gland - 5 Bar, for 19.00-36.00mm Cable, Pg36 Thread

Series Number : 93600

Status : Active

Product Category : Heavy-Duty Cable Glands

Engineering Part Number : 7000.6830.0




Documents and Resources

Drawings

[936000022_sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Contains Lead per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[CE - Declaration of Conformity](#)

[UKCA - Declaration of Conformity](#)

Part Details

General

| | |
|------------------|--|
| Status | Active |
| Category | Cable Glands |
| Series | 93600 |
| Description | Heavy-Duty Metal Cable Gland - 5 Bar, for 19.00-36.00mm Cable, Pg36 Thread |
| Cable Gland Type | IP68 - 5 Bar |
| IP Rating | IP68 |
| Product Name | Heavy-Duty Connectors |
| UPC | 887191822549 |

Physical

| | |
|-------------------------------|----------------|
| Cable Diameter | 19.00-36.00mm |
| Material - Cable Gland | Brass |
| Material - Plating | Nickel |
| Net Weight | 189.000/g |
| Packaging Type | Bag |
| Panel Cutout Diameter | 47.50mm |
| Temperature Range - Operating | -40° to +125°C |
| Thread Size | Pg36 |
| Thread Type | (Pg) |
| Waterproof / Dustproof | Yes |
| Waterproof / Dustproof Type | IP68 |

Mates With / Use With

Use with Part(s)

| | |
|-------------|---|
| Description | Part Number |
| Use With | Industrial connector hoods and housings |

This document was generated on May 09, 2026