

## FO cable - FOC-OE-OE-GZ04/... - 1411566

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fiber optic cable, multi-mode fiberglass 62.5/125 µm, OM1, length: various

### Why buy this product

- ✓ Satisfies UL 94, V0
- ✓ 2.8 mm single elements made from halogen-free and flame-retardant material

RoHS

### Key Commercial Data

Packing unit	1 STK
Custom tariff number	85447000
Country of origin	Germany

### Technical data

#### Standards and Regulations

Halogen-free	According to IEC 60754-2
Flammability rating according to UL 94	V0

### Classifications

eCl@ss

eCl@ss 5.1	27061803
eCl@ss 6.0	27069202
eCl@ss 8.0	27061803
eCl@ss 9.0	27061803

## FO cable - FOC-OE-OE-GZ04/... - 1411566

### Classifications

#### ETIM

ETIM 4.0	EC000830
ETIM 5.0	EC000034
ETIM 6.0	EC000034

#### UNSPSC

UNSPSC 13.2	26121607
-------------	----------

---

Phoenix Contact 2017 © - all rights reserved  
<http://www.phoenixcontact.com>