



4.9

14 Reviews



4.9

14 Reviews

Need Help?

[Browse All Products](#) | [Audio/Video Cables](#) | [Audio Cables](#) | [SPDIF Cables](#)



Roll over image to zoom in

1.5ft Velocity™ S/PDIF Digital Audio Coax Cable

Carries digital audio from a CD transport, DVD player, DAT deck or other digital component to an a/v receiver digital input or an outboard D/A converter input



4.9

14 Reviews

Product # : 40008

Connector 1 : (1) RCA Digital Audio Male

Connector 2 : (1) RCA Digital Audio Male

Lengths :

1.5ft

3ft

6ft

12ft

25ft

632 In Stock & ready to ship!



Add



Need it shipped today?

Place your order before the timer runs out!



print share chat

Product Info

Customer Reviews

Questions & Answers

Distributors

More Choices

Description

Features

Certifications

Specs

Product Description

The Velocity digital audio cable is a great upgrade to the cables typically included with consumer electronics products. The low-loss 75 Ohm oxygen-free copper center conductors and foam dielectric provide high quality digital sound and performance. The 100% aluminum foil and dual OFC braid shields protect against unwanted noise and interference.

Robustly constructed molded connectors attach to an ultra-flexible jacket, and enable easy installation and identification. The 24K gold-plated, durable connectors ensure long-lasting quality; fully molded connectors provide excellent strain relief.

Product Features

- Carries a digital audio signal
- Constructed from 75Ω oxygen-free copper
- Foil and braided shield to protect from interference

WARNING: Cancer and Reproductive Harm www.P65Warnings.ca.gov

Product Certifications



Product Specifications

Color :	Blue
Length :	1.50 Foot
UPC :	757120400080
Warranty :	Lifetime
Vendor :	C2G
Weight :	0.090 LB

Info

- About Us
- Order History
- Where To Buy
- More ▾

Service

- Contact Us
- OEM Solutions
- Tech Support
- More ▾

Resources

- Connector Guides
- ConnectXpress
- Drivers & Manuals
- More ▾

Have A Question?

- Get help with [Chat](#)
- Call C2G **800.506.9607**
- [f](#) [t](#) [v](#) [b](#)



United States | Europe +

Copyright © 2019 C2G. All Rights Reserved

