

Home

About

Contact Us

Help

Your Account

Shopping Cart - 0 items

Shop By Category

- Adapters
- Amphenol Connectors
- Audio Video Monitor Cables
- CAT-5e • CAT-6 • Telco Cables
- Coaxial Cables
- CX4 Cables • InfiniBand Cables
- DisplayPort Cables & Adapters
- D-Sub Cables • D-Sub Adapters
- Fiber Optic Patch Cables
- Fibre Channel & DIN Cables
- GPIO Cables (IEEE-488 Cables)
- HDMI Cables (High Speed HDMI)
- Power Cords
- QSFP Cables • QSFP+ Cables
- QSFP+ Modules & Loopbacks
- SAS Cables • SATA Cables
- SCSI Cables • VHDCI Cables
- SFP Cables • SFP Modules
- SFP+ Cables • SFP+ Modules
- B Cables

Shop By Application

- 20 Percent OFF CX4/SFP+/QSFP
- 30 Percent OFF CAT5e/CAT6/6a
- NEW 25 Percent OFF SALE
- Custom Cables & Cable Kits
- Data Center Cable Solutions
- Home Theater AV Cable Center
- Active Optical Cable Solutions

More ways to Shop

- Hot Items
- New Items

SFP+ Cables • SFP+ Modules » SFP+ Cables (Direct Attach) »

1m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable (3.3 ft)



[Click for larger image](#)

Amphenol 1m (3.3 ft) 10GbE SFP+ Direct Attach Copper Cables provide affordable 10-Gigabit Ethernet connectivity in a low-profile package. Each SFP+ cable utilizes an integrated 20-position "board-as-connector" design with zinc die-cast backshells for superior EMI performance and minimal insertion loss. Our 1m SFP+ cables are assembled with industry-leading 30 AWG twinaxial SKEWCLEAR® 2-pair wire; optimized for bandwidth-intensive applications such as 10Gb Ethernet, Fibre Channel, InfiniBand, and SONET. Full SFF-8431 SFP+ MSA compliance enhances compatibility with any standard SFP+ direct attach ported switch, router, or NIC. Special Notice: Cisco & HP brand SFP+ hardware will ONLY work with Cisco & HP brand SFP+ cables due to port-locking security features.

Product Features:

- 1 Week Only SALE -- 20% OFF SFP+ Cables with Coupon Code: HISPEED
- 1m (3.3ft) SFP+ 10GbE Direct Attach Passive Copper Cable by Amphenol
- Our OEM Equivalent SFP+ Cables Connect to any Security-Free SFP+ Port
- 30-Days 100% Satisfaction Guarantee with No Restocking Fees
- 10G Ethernet, Fibre Channel, InfiniBand & SONET multi-platform support
- Zinc die-cast SFF-8431 SFP+ connectors with push-to-release latching
- High performance quad-shielded 30 AWG twinaxial SKEWCLEAR wire
- Built and tested by industry leader Amphenol Interconnect Products
- Low cross-talk and pair-to-pair skew
- Fully compliant to the latest SFP Plus MSA (multi-source agreement)
- Exceeds 10-Gigabit Ethernet and 10G Fibre Channel performance standards
- Enjoy a reduced power budget and lower port cost compared to optical
- Consumes only .15W per end - 20X less power than 10GBASE-T
- Featuring our latest Rev. 2.0 SFP+ PCB for enhanced performance
- Guaranteed to cross reference with the following brands:
- Tyco: 2032237-2 / 2032247-2 / 2053649-2
- Molex: 74752-1101 / 74752-2101
- Methode: DM-255-100
- Gore: SFN8200-1
- Dell: 330-3965
- Amphenol: SF-SFPP2XPASS-001
- Interested in larger volumes or custom lengths? Call 1-866-223-2860

Similar Products

[0.5m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable \(1.6 ft\)](#)



[10m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable \(32.8 ft\)](#)



[2m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable \(6.6 ft\)](#)



[3m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable \(9.8 ft\)](#)



[5m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable \(16.4 ft\)](#)



[7m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable \(23 ft\)](#)



[8.5m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable \(27.9 ft\)](#)



Item#	Color	Length	Qty 1-50	Qty >50	Availability	Order Qty
(SF-SFPP2EPASS-001 B		1m (3.3ft)				

Add all entered quantities to cart - >

[Same Day Shipping](#)



[8m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable \(26.2 ft\)](#)



Sign up for our E-
mail Newsletter

Privacy by  SafeSubscribeSM