


Technical data sheet

Article number:
170-10600

HEGP06



Product Group	Standard polyester braided sleeving
Product Family	Helagaine HEGP
Material	Polyester (PET)
Colour	Black (BK)
Application Method	To prevent fraying, the sleeve can be cut with the hot cutting tool HSG0, see page
Bundle Ø max.	11 mm
Bundle Ø min.	4 mm
Melting Point	+250 °C
Operating Temperature	-50 °C to +150 °C
Package Content	100 m
Package Content packed in	meter
Specifications	ECE R-118-03 Abschnitt 6 / Annex 6, ECE R-118-03 Abschnitt 8 / Annex 8, EN 45545-2

HF ✓ RoHS ✓

EN 45545-2 **ECE R-118**