





Item	Code	Spec	
NO of PIN	N	20	
Pitch	P	1.0±0.07	
Total Length	L	102±1.5	
Margin	M	1.0±0.07	
Thickness	T	0.3±0.03	
Strip Length	S1	3.5±0.5	
	S2	3.5±0.5	
Supporting Length	D1	6.0±1.0	
	D2	6.0±1.0	
Total Pitch	TP	19.0±0.08	
Total Width	W	21.0±0.08	
Conductors	Width	0.65±0.03	
	Thickness	0.05±0.005	
	Plated	Sn(1um)	Min
Film	White		0.06mm
	White		0.06mm
Supporting	Blue		0.225mm
UL NO.	UL20890(105℃ 90V)		

Processing requirement:

1.			
NO.	Specification description	Number	Remarks



CnC Tech, LLC

Industrial Cable and Connector Technology

DRAWN BY:	DATE: 2018/07/20	DESCRIPTION: 20-102-1. 0-3. 5/3. 5-6/6-A-Tin		
CHECKED BY:	SHEET 1 of 1	ITEM NO. 311-20-0102		
APPROVED BY:	SCALE 1:1	REV. A/0	UNIT: mm	