



**Part Number :** [936010693](#)

**Product Description :** Heavy-Duty Harsh Environment (HE) Single Lever Hood, Die-cast Aluminum, with 1 Lever, Top Entry, Size 3A «21x21», M20 Thread, Black

**Series Number :** 93601

**Status :** Active

**Product Category :** Heavy-Duty Connectors

**Engineering Number :** 7803.6232.1




---

## Documents & Resources

---

### Product Environment Compliance

#### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

#### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

**Part Details**

**General**

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Harsh Environment (HE) Single Lever Hood, Die-cast Aluminum, with 1 Lever, Top Entry, Size 3A «21x21», M20 Thread, Black
Comments	IP67 with screw gasket.
Component Type	Single Lever Hood
IP Rating	IP66
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	HE
UPC	887191842806

**Agency**

CSA	256883
UL	E249674

**Electrical**

Voltage - Maximum	230V / 400V
-------------------	-------------

**Physical**

Component Size	3A «21x21»
Entry Location	Top
Hood Coating	Polyester Powder
Hood Color	Black RAL 9005
Lock to Mating Part	Yes

Material - Hood	Die-cast Aluminum
Material - Lever	Stainless Steel
Net Weight	29.160/g
Number of Levers	1
Packaging Type	Bag
Thread Size	M20
Thread Type	(M) Metric

## Mates With / Use With

### Use with Part(s)

Description	Part Number
Use With	Size 3A «21x21» S-A, S-D, and S-Q Inserts

---

This document was generated on Sep 25, 2025