



CT30125C00, Cable Tie, 1.25" Bundle, 30 Lb Tensile, UV Black

By Burndy
Catalog # [CT30125C00](#)

Nylon cable ties, Tensile strength-30 Lbs, Color- UV Black, 05.84"L, 0.14"W, 01.25" Bundle Dia.



Features

Standard Cable Tie

General

Catalog Number	CT30125C00
Color	UV Black (Mil. Spec.)
Material	NYLON 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	30
Tool Type	Intermediate
Trade Name	UNIRAP™
UPC	781810332283

Dimensions

Dimension - Bundle Diameter Max inch	1.25 in
Dimension - L Length Overall mm	146 mm
Dimension - Length Overall inch	5.75 in
Dimension - Width inch	0.14 in
Dimension - Width mm	3.6 mm

Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-5-0
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	100
Packaging Type	Bag

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section G - Wire Management](#)
[Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
[Sales Drawings - 50080813](#)



A proud member of the Hubbell Family.