

Female quick-connect terminal, 14.2 mm x 4.16 mm



Description

With snap-in tongue to snap into group connection plug. Tin-plated socket standardized according to A2.8-0.8 DIN 46 340 MS.

Flat cable lug bush suitable for RAFI Female quick-connect terminal 2.8 x 0.8 mm.

technical data

› general

Packaging unit	100 pcs.
Net weight	0.2 g
Minimum order quantity (MOQ)	100 pcs.
RoHS compliant	Yes
REACH compliant	Yes
Country of origin	DE

direct links

› RAFI eCatalog

› mounting diameters

Outside dimension, length	14.2 mm
Outside dimension, width	4.16 mm
Outside dimension, height	4.73 mm

› mechanical data

Terminal on the rear	Flat quick-connect terminal 2.8 x 0.8 tin-plated
----------------------	--

› electrical data

AWG max.	1.5 mm ²
AWG min.	0.5 mm ²

The information in this data sheet only contains general descriptions and / or performance features, which may not apply precisely as described to the respective application, and which may change due to further product enhancements. The technical data, illustrations and other information about our products are the mere results of individual technical testing. These descriptions and other product features are only binding if they are expressly agreed upon at the time of the conclusion of a binding contract. In all other cases, we reserve the right to make technical changes as well as changes of availability. Pictures and other graphic illustrations are approximations only. All product names may be trademarks or brand names of the RAFI Group or any other sub-supplier of RAFI. The use of such by any third parties for their own purposes may infringe the rights of the respective entity holding those rights.

date: Sep 19, 2025 page: 1/1

RAFI GmbH & Co. KG

Ravensburger Str. 128-134
88276 Berg / Ravensburg
Germany
www.rafi-group.com,
info.headquarters@rafi-group.com