

插頭部件 (Plug Component)			頭部剥皮尺寸 (Plug strip dimension)			線材規格(Wire Spec.)	尾部剥皮尺寸 (Terminal roj & Strip)			尾部處理 (Terminal Component)		
顏色(Color)	零件描述(Component)	數量(Q'ty)	內制(Strip)	外制(Roj)	顏色(Color)		外制(Roj)	內制(Strip)	顏色(Color)	顏色(Color)	零件描述(Component)	數量(Q'ty)
35P紅色 90A+2A Red 鍍鎳 Nickel-Plated	ME-301 (10A 125V-) (NEMA 5-15P) Ø4.75 圓管端子 (Earth Pin Terminal)	1	5 ⁺¹ ₋₀	23±1	黑/Black(L)	SJT 18AWG/3C 105°C 紅色(Red) 線長: (Length) 1828.8 ^{+50.8} _{-12.7}	16±1	5 ⁺¹ ₋₀	黑/Black(L)	35P紅色 90A+2A Red 銅本色 (Copper)	ME-302 (10A 125V-) (IEC 320 C-13) 電腦電源線端子 GEN#987458S-0 Computer power cord terminals	1
鍍鎳 Nickel-Plated	6.3*1.5 單片圓頭端子 (Solid Blades)	2	5 ⁺¹ ₋₀	23±1	白/White(N)		16±1	5 ⁺¹ ₋₀	白/White(N)	白色(White)	ME-302兩件式內模 (ME-302 Inner Body)	3
白色(White)	301單件式內模 (301 Inner Body)	1			綠/Green(E)		16±1	5 ⁺¹ ₋₀	綠/Green(E)			1

插頭端面圖
(Dimensions of Plug Face)

15±0.15

1828.8^{+50.8}_{-12.7}

12.7±0.15

Insulation Thickness 0.76 mm
Overall Diameter 2.7±0.10 mm

Copper Conductor
41/0.160±0.004 mm
Resistance 22.4
(20°C (Max), ohms/km)

Jacket Thickness 0.76 mm
Overall Diameter 7.8±0.15 mm

線材截面圖
(Wire Cross-Section)

Green
White
Black

包裝方式(Packing)

扎線方式 (Bulk Pack)	每 10 條一扎 Per 10 pcs/Ties
紙箱尺寸 (Carton Size)	480 X 320 X 250
包裝數量 (Packing Q'ty)	PCS
標籤(Label)	UL Detachable Label
正側事項 (Carton Print)	依客戶要求印刷 (See Purchase Order)

1. 高壓測試:1500V/1Sec <1mA
(Hi-Pot Test:1500v/1Sec <1mA)

電線印字內容 Wire Printed	使用充實線材 凹印字 (Un-Filler, Gravure)	紙箱事項標碼 Shipping Mark
V E322763 (UL) SJT 18AWG(0.824mm²)x3C VW-1 105°C 300V /ET c(UL) SJT 18AWG(0.824mm²)x3C FT2 105°C 300V -LF- (UL) SJT 18AWG(0.824mm²)x3C VW-1 105°C 300V E77975 WONDERFUL-D CSA SJT 18AWG(0.824mm²)x3C FT2 105°C 300V 1143774 -F- -LF-		CnC

SIGNATURE	NAME	DATE
APPROVED		
M.F.G. CHECKED		
Q.A. CHECKED		
DRAWN	楊承正	2011.11.21

SIZE: A4	UNIT: mm	SCALE: 1:1	PROJ.
----------	----------	------------	-------

CUSTOMER	CnC Tech, LLC Industrial Cable and Connector Technology
----------	--

2011.11.21	新版發行	楊承正
REV DATE	DESCRIPTION	SYMBOL
PART No.	800-18-13D-RE-0006F	
DWG No.		