



Pushing Performance  
Since 1945

# har-SAB M8/8/3p M12/12p w/o LED



Part number	09 07 006 2010 000
Specification	har-SAB M8/8/3p M12/12p w/o LED
HARTING eCatalogue	<a href="https://b2b.harting.com/09070062010000">https://b2b.harting.com/09070062010000</a>

## Version

Total number of ports	8
Number of contacts	3

## Technical characteristics

Rated current	1 A
Rated voltage	10 V DC 30 V DC
Limiting temperature	-25 ... +85 °C
Degree of protection acc. to IEC 60529	IP67
Number of channels per port	2
Circuit logic	PNP

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Commercial data

Packaging size	1
----------------	---



Pushing Performance  
Since 1945

Commercial data

Country of origin	China
European customs tariff number	85444290
GTIN	5713140276741
eCl@ss	27440108 Passive Sensor-Actuator-Interface (with cable)